

SDIK PZ2 X 100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated crosshead screwdriver type Pozidriv SDIK
PZ DIN 7438, ISO 8764/2-PZ, output to ISO 8764-PZ,
SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2
Order No.	2749930000
Type	SDIK PZ2 X 100
GTIN (EAN)	4050118897234
Qty.	1 pc(s).

SDIK PZ2 X 100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Width	215 mm	Width (inches)	8.465 inch
Net weight	94 g		

Technical data

Description of article	VDE-insulated crosshead screwdriver, Pozidrive size 2	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade length	100 mm	Blade size, crosshead	2
Blade width (B)	2 mm	Form	Pozidrive, round
Size	2		

Classifications

ETIM 6.0	EC000144	ETIM 7.0	EC000144
ETIM 8.0	EC000144	ETIM 9.0	EC000144
ECLASS 9.0	21-04-04-06	ECLASS 9.1	21-04-04-06
ECLASS 10.0	21-04-04-06	ECLASS 11.0	21-04-04-06
ECLASS 12.0	21-04-04-06	ECLASS 13.0	21-04-04-06
ECLASS 14.0	21-04-04-06		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141
RoHS Compliance Status	Not affected

Downloads

Catalogues	Catalogues in PDF-format
------------	--