

SD EL 0.3X1.5X40 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 1.5 mm, Blade length: 40 mm, Blade thickness (A): 0.3 mm
Order No.	2750060000
Type	SD EL 0.3X1.5X40 PICO
GTIN (EAN)	4050118897548
Qty.	1 pc(s).

SD EL 0.3X1.5X40 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	140 mm	Length (inches)	5.512 inch
Net weight	20 g		

Technical data

Version	straight
---------	----------

Screwing tools

Blade length	40 mm	Blade thickness (A)	0.3 mm
Blade width (B)	1.5 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07