

**SD EL 0.4X2.5X75 PICO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Slotted screwdriver with rounded blade SD DIN 5265,  
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-  
Top tip, SoftFinish grip

**General ordering data**

Version	Screwdriver, Blade width (B): 2.5 mm, Blade length: 75 mm, Blade thickness (A): 0.4 mm
Order No.	<a href="#">2750080000</a>
Type	SD EL 0.4X2.5X75 PICO
GTIN (EAN)	4050118897562
Qty.	1 pc(s).

**SD EL 0.4X2.5X75 PICO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	175 mm	Length (inches)	6.89 inch
Net weight	20 g		

**Technical data**

Description of article	Screwdriver with slotted bit, 0.4 x 2.5	Version	straight
------------------------	---	---------	----------

**Screwing tools**

Blade length	75 mm	Blade thickness (A)	0.4 mm
Blade width (B)	2.5 mm	Form	Slotted

**Classifications**

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07
ECLASS 14.0	21-04-04-07		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Not affected