

SD EL 0.4X2.5X75 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 2.5 mm, Blade length: 75 mm, Blade thickness (A): 0.4 mm
Order No.	2750080000
Type	SD EL 0.4X2.5X75 PICO
GTIN (EAN)	4050118897562
Qty.	1 pc(s).

SD EL 0.4X2.5X75 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	175 mm	Length (inches)	6.89 inch
Net weight	20 g		

Technical data

Description of article	Screwdriver with slotted bit, 0.4 x 2.5	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade length	75 mm	Blade thickness (A)	0.4 mm
Blade width (B)	2.5 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07