

SD EL 0,6X3,5X100 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade thickness (A): 0.6 mm
Order No.	2750100000
Type	SD EL 0,6X3,5X100 PICO
GTIN (EAN)	4050118897586
Qty.	1 pc(s).

SD EL 0,6X3,5X100 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	200 mm	Length (inches)	7.874 inch
Net weight	18 g		

Technical data

Description of article	Screwdriver with slotted bit, 0.6 x 3.5	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.6 mm
Blade width (B)	3.5 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07
ECLASS 14.0	21-04-04-07		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Not affected

Downloads

Catalogues	Catalogues in PDF-format
------------	--