

SD EL 0.8X4.0X100 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 4 mm, Blade length: 100 mm, Blade thickness (A): 0.8 mm
Order No.	2750110000
Type	SD EL 0.8X4.0X100 PICO
GTIN (EAN)	4050118897593
Qty.	1 pc(s).

SD EL 0.8X4.0X100 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	200 mm	Length (inches)	7.874 inch
Net weight	20 g		

Technical data

Version	straight
---------	----------

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.8 mm
Blade width (B)	4 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07
ECLASS 14.0	21-04-04-07		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%