

**KCMA-42-300-5A-2.5VA-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image, Similar to illustration**

Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

**General ordering data**

|              |   |
|--------------|---|
| Version      | Primary current: 300 A, Secondary current max.: 5 A, Load: 2.5 VA, Tolerance class: 1, Split-core current transformer |
| Order No.    | <a href="#">2753230000</a>  |
| Type         | KCMA-42-300-5A-2.5VA-1  |
| GTIN (EAN)   | 4050118896251   |
| Qty.         | 1 pc(s).  |
| Manufacturer | MBS AG  |

Creation date July 5, 2024 3:24:11 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

**KCMA-42-300-5A-2.5VA-1****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 69 mm | Depth (inches)  | 2.717 inch |
| Height     | 96 mm | Height (inches) | 3.78 inch  |
| Width      | 67 mm | Width (inches)  | 2.638 inch |
| Net weight | 362 g |                 |            |

**Temperatures**

|                       |               |
|-----------------------|---------------|
| Operating temperature | -5 °C...50 °C |
|-----------------------|---------------|

**Dimensions of live conductors**

|                       |                          |                 |       |
|-----------------------|--------------------------|-----------------|-------|
| Type of conductor     | Insulated conductor only | Round conductor | 42 mm |
| Installation location | Indoor use               |                 |       |

**Electrical attributes**

|                   |         |                 |       |
|-------------------|---------|-----------------|-------|
| Load              | 2.5 VA  | Primary current | 300 A |
| Secondary current | 0...5 A | Tolerance class | 1     |

**Technical properties**

|              |       |                   |      |
|--------------|-------|-------------------|------|
| Cable length | 2.5 m | Protection degree | IP20 |
|--------------|-------|-------------------|------|

**Insulation coordination**

|                 |   |
|-----------------|---|
| Tolerance class | 1 |
|-----------------|---|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002048    | ETIM 7.0    | EC002048    |
| ETIM 8.0    | EC002048    | ETIM 9.0    | EC002048    |
| ECLASS 9.0  | 27-21-09-02 | ECLASS 9.1  | 27-21-09-02 |
| ECLASS 10.0 | 27-21-09-02 | ECLASS 11.0 | 27-21-09-02 |
| ECLASS 12.0 | 27-21-09-02 | ECLASS 13.0 | 27-21-09-02 |

**Environmental Product Compliance**

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">EU Declaration of Conformity</a> |
| User Documentation                          | <a href="#">Instruction sheet German</a>     |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>     |

## KCMA-42-300-5A-2.5VA-1

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

