

KCMA-42-600-5A-2.5VA-0.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image, Similar to illustration**

Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 600 A, Secondary current max.: 5 A, Load: 2.5 VA, Tolerance class: 0,5, Split-core current transformer
Order No.	2753260000
Type	KCMA-42-600-5A-2.5VA-0.5
GTIN (EAN)	4050118896688
Qty.	1 pc(s).
Manufacturer	MBS AG

Creation date July 14, 2024 3:12:56 PM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

KCMA-42-600-5A-2.5VA-0.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	69 mm	Depth (inches)	2.717 inch
Height	96 mm	Height (inches)	3.78 inch
Width	67 mm	Width (inches)	2.638 inch
Net weight	427 g		

Temperatures

Operating temperature	-5 °C...50 °C
-----------------------	---------------

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	42 mm
Installation location	Indoor use		

Electrical attributes

Load	2.5 VA	Primary current	600 A
Secondary current	0...5 A	Tolerance class	0,5

Technical properties

Cable length	0.5 m	Protection degree	IP20
--------------	-------	-------------------	------

Insulation coordination

Tolerance class	0,5
-----------------	-----

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ETIM 9.0	EC002048
ECLASS 9.0	27-21-09-02	ECLASS 9.1	27-21-09-02
ECLASS 10.0	27-21-09-02	ECLASS 11.0	27-21-09-02
ECLASS 12.0	27-21-09-02	ECLASS 13.0	27-21-09-02

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Catalogues	Catalogues in PDF-format

KCMA-42-600-5A-2.5VA-0.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

