

SAIH-PB-2X0.34-PVC-500**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller offers a large and comprehensive range of sensor-actuator cables. We provide both, sensor cables as well as bus and valve cables of various sizes and lengths. If you cannot find a specific product or a product in the desired length, just contact us.

General ordering data

Version	Bus line, Number of poles: 2, 500 m, Shielded: Yes, LED: No, Sheath material: PVC, Halogen: No, Yes
Order No.	2764920000
Type	SAIH-PB-2X0.34-PVC-500
GTIN (EAN)	4064675031222
Qty.	1 pc(s).
Packaging	on plywood reel

SAIH-PB-2X0.34-PVC-500

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	60 g
------------	------

Technical specifications for cable

Bending radius, min., moving	9 x cable diameter	Bending radius, min., stationary	18 x cable diameter
Cable length	500 m	Colour coding	red, green
Core cross-section	0.34 mm ²	Halogen	No, Yes
Insulation	TPM, PVC	Number of poles	2
Number of wires	2	Outside diameter	7.8 mm ± 0.2 mm
Resistance to oils	Yes	Resistant to welding beads	No
Sheath material	PVC	Sheathing colour	violet
Shielded	Yes	Suitable for cable carriers	No
Temperature range, moving	-5...60 °C	Temperature range, stationary	-20...70 °C
Torsion resistance	0 °/m	Welding spark resistance	No

Cable structure

Colour coding	red, green	Insulation	TPM, PVC
Number of wires	2	Sheathing colour	violet

Mechanical and material properties of cable

Colour	red, green	Halogen	No, Yes
Resistance to oils	Yes	Torsion resistance	0 °/m

Classifications

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ETIM 9.0	EC003249
ECLASS 9.0	27-06-18-05	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-18-01	ECLASS 11.0	27-06-18-01
ECLASS 12.0	27-06-18-01	ECLASS 13.0	27-06-18-01

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--