

**DRW373900LT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

Individual relays within the D-SERIES DRW

- 3 CO contacts
- Optional AC or DC coils
- With test button and Integrated status LED

**General ordering data**

|            |   |
|------------|---|
| Version    | D-SERIES DRW / DRH, Relay, Number of contacts: 3, CO contact AgSnO, Rated control voltage: 400 V AC, Continuous current: 16 A, Flat blade connections (4.8 mm x 0.5 mm), Test button available: Yes |
| Order No.  | <a href="#">2765580000</a>  |
| Type       | DRW373900LT   |
| GTIN (EAN) | 4064675076612   |
| Qty.       | 10 pc(s).   |

Creation date July 3, 2024 5:48:09 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

**DRW373900LT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Depth      | 48 mm  | Depth (inches)  | 1.89 inch  |
| Height     | 36 mm  | Height (inches) | 1.417 inch |
| Width      | 36 mm  | Width (inches)  | 1.417 inch |
| Net weight | 84.4 g |                 |            |

**Temperatures**

|                     |   |                       |                |
|---------------------|---|-----------------------|----------------|
| Storage temperature | -40 °C...60 °C                          | Operating temperature | -40 °C...60 °C |
| Humidity            | 5...85 % rel. humidity, no condensation |                       |                |

**Rated data UL**

|                         |         |
|-------------------------|---------|
| Certificate No. (cURus) | E312083 |
|-------------------------|---------|

**Control side**

|                       |          |                  |                         |
|-----------------------|----------|------------------|-------------------------|
| Rated control voltage | 400 V AC | Rated current AC | 6.1 mA                  |
| Power rating          | 2.5 VA   | Coil resistance  | 26000 $\Omega \pm 10\%$ |
| Coil tolerance        | 10 %     | Status indicator | red LED                 |

**Load side**

|   |                      |   |                                       |
|---|----------------------|---|---------------------------------------|
| Rated switching voltage                 | 400 VAC              | Continuous current                      | 16 A                                  |
| Max. switching frequency at rated load  | 0.1 Hz               | Max. switching voltage, AC              | 400 V                                 |
| Max. switching voltage, DC              | 250 V                | Inrush current                          | 80 A / 50 ms                          |
| AC switching capacity (resistive), max. | 6400 VA              | DC switching capacity (resistive), max. | 384 W @ 24 V                          |
| Switch-on delay                         | < 20 ms              | Switch-off delay                        | < 20 ms                               |
| Contact type                            | 3 CO contact (AgSnO) | Mechanical service life                 | 20 x 10 <sup>6</sup> switching cycles |
| Min. switching power                    | 100 mA @ 12 V        |   |                                       |

**General data**

|                                      |   |                        |
|--------------------------------------|---|------------------------|
| Test button available                | Yes   |                        |
| Version of test button               | Lockable test button, Momentary test button |                        |
| Mechanical switch position indicator | Yes   |                        |
| Colour                               | Transparent                                 |                        |
| UL94 flammability rating component   | Component                                   | Relay test button      |
|                                      | UL94 flammability rating                    | HB                     |
|                                      | Component                                   | Relay status indicator |
|                                      | UL94 flammability rating                    | HB                     |
|                                      | Component                                   | Relay baseplate        |
|                                      | UL94 flammability rating                    | V-0                    |
|                                      | Component                                   | Relay cover            |
|                                      | UL94 flammability rating                    | V-2                    |

## DRW373900LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Insulation coordination

|  |                                |   |                              |
|--|--------------------------------|---|------------------------------|
| Insulation coordination according to             | EN 61810-1:2008                | Rated voltage   | 400 V                        |
| Pollution severity                               | 3                              | Surge voltage category  | III                          |
| Insulating material group                        | IIIa                           | Clearance and creepage distances for control side - load side | ≥ 6,3 mm                     |
| Dielectric strength for control side - load side | 4 kV <sub>eff</sub> / 1 Min.   | Dielectric strength of neighbouring contacts                  | 4 kV <sub>eff</sub> / 1 Min. |
| Dielectric strength of open contact              | 2.5 kV <sub>eff</sub> / 1 Min. | Protection degree   | IP20                         |

## Further details of approvals / standards

|                         |         |
|-------------------------|---------|
| Certificate No. (cURus) | E312083 |
|-------------------------|---------|

## Connection data

|                        |   |
|------------------------|---|
| Wire connection method | Flat blade connections<br>(4.8 mm x 0.5 mm) |
|------------------------|---|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001437    | ETIM 7.0    | EC001437    |
| ETIM 8.0    | EC001437    | ETIM 9.0    | EC001437    |
| ECLASS 9.0  | 27-37-16-01 | ECLASS 9.1  | 27-37-16-01 |
| ECLASS 10.0 | 27-37-16-01 | ECLASS 11.0 | 27-37-16-01 |
| ECLASS 12.0 | 27-37-16-01 | ECLASS 13.0 | 27-37-16-01 |

## Environmental Product Compliance

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

## Approvals

Approvals




|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E312083    |

## Downloads


|   |   |
|---|---|
| Approval/Certificate/Document of Conformity | <a href="#">EU Konformitätserklärung / EU Declaration of Conformity</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>   |
| User Documentation                          | <a href="#">FL D-SERIES DRW3CO_LOAD_GUIDE</a>                           |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                |

## Drawings


### Wiring diagram




### Graph




### Dimensional drawing



### Graph



### Graph



**DRW373900LT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Test button cover**

Test button cover for the D-SERIES DRW/DRH relays.

**General ordering data**

|            |                            |                                       |
|------------|----------------------------|---------------------------------------|
| Type       | TEST LEVER BLOCK DRH/DRW   | Version                               |
| Order No.  | <a href="#">7760056249</a> | D-SERIES DRW / DRH, Test button cover |
| GTIN (EAN) | 6944169641626              |                                       |
| Qty.       | 10 pc(s).                  |                                       |

**Retaining clips**

Retaining clip for D-SERIES DRW/DRH relays

- Metal retaining clip

**General ordering data**

|            |                            |                                    |
|------------|----------------------------|------------------------------------|
| Type       | DRW/DRH CLIP M             | Version                            |
| Order No.  | <a href="#">1220260000</a> | D-SERIES DRW / DRH, Retaining clip |
| GTIN (EAN) | 4032248999576              |                                    |
| Qty.       | 10 pc(s).                  |                                    |

## DRW373900LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | ESG 9/11 K MC NE WS        | Version  |
| Order No.  | <a href="#">1857440000</a> | ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive |
| GTIN (EAN) | 4032248402731              |  |
| Qty.       | 200 pc(s).                 |  |

## Blank, adhesive backing



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |  |
|------------|----------------------------|--|
| Type       | SM 18/9.5 K MC NE WS       | Version  |
| Order No.  | <a href="#">1248580000</a> | SwitchMark, Device markers, 9.5 x 18 mm, white |
| GTIN (EAN) | 4050118038965              |  |
| Qty.       | 200 pc(s).                 |  |

## DRW373900LT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |   |
|------------|----------------------------|---|
| Type       | SM 18/9.5 K MC NE GR       | Version   |
| Order No.  | <a href="#">1248610000</a> | SwitchMark, Device markers, 9.5 x 18 mm, grey                 |
| GTIN (EAN) | 4050118038675              |   |
| Qty.       | 200 pc(s).                 |   |
| Type       | SM 18/9.5 K MC NE GE       | Version   |
| Order No.  | <a href="#">1248590000</a> | SwitchMark, Device markers, 9.5 x 18 mm, Siemens 3 SB, yellow |
| GTIN (EAN) | 4050118038958              |   |
| Qty.       | 200 pc(s).                 |   |

## Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | ESG 6/17 K MC NE WS        | Version   |
| Order No.  | <a href="#">1880120000</a> | ESG, Device markers x 17 mm, PA 66, Colour: white, Self-adhesive  |
| GTIN (EAN) | 4032248478804              |   |
| Qty.       | 200 pc(s).                 |   |
| Type       | ESG 6/17 K MC NE GE        | Version   |
| Order No.  | <a href="#">1880110000</a> | ESG, Device markers x 17 mm, PA 66, Colour: yellow, Self-adhesive |
| GTIN (EAN) | 4032248478798              |   |
| Qty.       | 200 pc(s).                 |   |

**DRW373900LT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****ESG 6/17****Guaranteed long service life: ESG**

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

**Your benefits with MultiMark**

- "Different materials for various requirements"
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

|            |                            |                                       |
|------------|----------------------------|---------------------------------------|
| Type       | ESG 6/17 MM WS             | Version                               |
| Order No.  | <a href="#">2005100000</a> | ESG, Device markers, 6 x 17 mm, white |
| GTIN (EAN) | 4050118390728              |                                       |
| Qty.       | 3,000 pc(s).               |                                       |

**Sockets**

Relay sockets for the D-SERIES DRW/DRH relays

- Up to 3 CO contacts
- Screw connection

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | SPW ECO 3CO                | Version   |
| Order No.  | <a href="#">1220250000</a> | D-SERIES DRW / DRH, Relay socket, Number of contacts: 3, CO |
| GTIN (EAN) | 4032248100101              | contact, Continuous current: 16 A, Screw connection         |
| Qty.       | 10 pc(s).                  |   |



**DRW373900LT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**


|            |                            |   |
|------------|----------------------------|---|
| Type       | ESG 6/15 K MC NE WS        | Version   |
| Order No.  | <a href="#">1880100000</a> | ESG, Device markers x 15 mm, PA 66, Colour: white, Self-adhesive  |
| GTIN (EAN) | 4032248478781              |   |
| Qty.       | 200 pc(s).                 |   |
| Type       | ESG 6/15 K MC NE GE        | Version   |
| Order No.  | <a href="#">1880130000</a> | ESG, Device markers x 15 mm, PA 66, Colour: yellow, Self-adhesive |
| GTIN (EAN) | 4032248478910              |   |
| Qty.       | 200 pc(s).                 |   |

DRW373900LT

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
  
www.weidmueller.com

Drawings

Miscellaneous



Type codes