

IE-SFP-1GE-RJ45**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Features of SFP-Transceiver series**

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

General ordering data

Version	SFP Transceiver, 10/100/1000 MBit/s, RJ45, 100 m, -40 °C...85 °C
Order No.	2766120000
Type	IE-SFP-1GE-RJ45
GTIN (EAN)	4064675023791
Qty.	1 pc(s).

IE-SFP-1GE-RJ45**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	18 g
------------	------

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

EMC conformity and approvals

EMC standards	EN 55032, EN 55035	Safety standard	UL 62368-1
---------------	--------------------	-----------------	------------

Environmental conditions

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	10/100/1000 MBit/s	Digital diagnostic monitor function (DDM)	Not supported
Connector type	RJ45	Transmission distance, typ.	100 m
Note	10/100/1000BASE T operation requires the host system to have an SGMII interface with no clocks, and the SFP copper module PHY Interface to be configured by the host system. With a SERDES interface that does not support SGMII, the module will operate at 1000BASE T only.		

Guarantee

Time interval	3 years
---------------	---------

Interfaces

RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-duplex mode, Auto MDI/MDI-X port
------------	--

Power supply

Voltage supply	3.3 V (via Ethernet switch)
----------------	-----------------------------

Technical data

Type of mounting	Insert in SFP slot
------------------	--------------------

IE-SFP-1GE-RJ45**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC003628	ETIM 9.0	EC003628
ECLASS 9.1	27-44-02-92	ECLASS 10.0	27-44-02-92
ECLASS 11.0	19-17-03-03	ECLASS 12.0	19-17-03-03
ECLASS 13.0	19-17-03-03		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity RCM Declaration of Conformity UK Declaration of Conformity
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format