

**VGM32-MS65 4X8 SL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	Cable glands, Cable glands, M 32, 7.5 mm, Brass, nickel-plated
Order No.	<a href="#">2784950000</a>
Type	VGM32-MS65 4X8 SL
GTIN (EAN)	4064675061526
Qty.	25 pc(s).

**VGM32-MS65 4X8 SL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	43.34 g
------------	---------

**Temperatures**

Operating temperature	-40 °C... 135 °C
-----------------------	------------------

**General information**

AF size	36 mm	Cable glands	M 32
External thread	M 32	Length of thread	7.5 mm
Material	Brass, nickel-plated	Notch multi-layer sealing diameter 1	8 mm
Notch multi-layer sealing diameter 2	8 mm	Notch multi-layer sealing diameter 3	8 mm
Notch multi-layer sealing diameter 4	8 mm	Protection degree	IP65
Seal insert	TPE	UL 94 flammability rating	V-0
Width, outer dimension C	38.5 mm		

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

**VGM32-MS65 4X8 SL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



## VGM32-MS65 4X8 SL

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### IP65 multi wire sealing

### General ordering data

Type	VB 8.0X20 BK	Version
Order No.	<a href="#">2784920000</a>	Cable glands, Cable glands
GTIN (EAN)	4064675061403	
Qty.	100 pc(s).	