

IE-ANT-CELL-SISO-EO-SMAM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Version	Omni-directional antenna, Cellular antenna, Up to 5G (support for frequencies below 2.7 GHz, e.g., bands n1, n2, n28), Vertical, SMA male, IP66, Impedance: 50 Ω
Order No.	2788130000
Type	IE-ANT-CELL-SISO-EO-SMAM
GTIN (EAN)	4064675066392
Qty.	1 pc(s).

Creation date August 24, 2024 4:55:56 AM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

IE-ANT-CELL-SISO-EO-SMAM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	208 mm	Height (inches)	8.189 inch
Net weight	46.58 g		

Temperatures

Storage temperature	-40 °C...75 °C	Operating temperature	-40 °C...75 °C
---------------------	----------------	-----------------------	----------------

Enclosure material

Colour	black
--------	-------

Included in delivery

Included in delivery	1 x antenna
----------------------	-------------

Technical data

Antenna gain	2 dBi	Composite power max.	10 W
Frequency range	690-950 MHz, 1.7-3.8 GHz	Impedance	50 Ω
Polarisation	Vertical	Standing wave ratio	1.5 typical / 2.0 max
Type of connection	SMA male		

Environmental conditions

Operating temperature, max.	75 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	75 °C	Storage temperature, min.	-40 °C

Classifications

ETIM 6.0	EC001698	ETIM 7.0	EC001698
ETIM 8.0	EC001698	ETIM 9.0	EC001698
ECLASS 9.1	19-07-01-90	ECLASS 10.0	19-07-01-07
ECLASS 11.0	19-07-01-07	ECLASS 12.0	19-07-01-07
ECLASS 13.0	19-07-01-07	ECLASS 14.0	19-07-01-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Technical Documentation	Radiation Pattern
User Documentation	Hardware Installation Guide
Catalogues	Catalogues in PDF-format

IE-ANT-CELL-SISO-EO-SMAM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Antennas and antenna accessories (coax cables and mounts)****Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

General ordering data

Type	IE-CC-SMAM-SMAF-3M	Version
Order No.	2787930000	Antenna cable, Connection 1: SMA male, Connection 2: SMA female,
GTIN (EAN)	4064675066095	Length: 3 m
Qty.	1 pc(s).	
Type	IE-CC-SMAM-SMAF-1M	Version
Order No.	2787920000	Antenna cable, Connection 1: SMA male, Connection 2: SMA female,
GTIN (EAN)	4064675066088	Length: 1 m
Qty.	1 pc(s).	
Type	IE-CC-SMAM-SMAF-5M	Version
Order No.	2787940000	Antenna cable, Connection 1: SMA male, Connection 2: SMA female,
GTIN (EAN)	4064675066200	Length: 5 m
Qty.	1 pc(s).	