

SCT 4.6/520**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Version	Cable ties, 4.6 x 520 mm, Stainless steel 1.4404 (316L), 778 N
Order No.	2791420000
Type	SCT 4.6/520
GTIN (EAN)	4064675070948
Qty.	100 pc(s).

SCT 4.6/520

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.26 mm	Depth (inches)	0.01 inch
Height	520 mm	Height (inches)	20.472 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	5.62 g		

Temperatures

Operating temperature range	-40...300 °C	Installation temperature	-40
-----------------------------	--------------	--------------------------	-----

Installation materials

Bundle diameter, max.	150 mm	Bundle diameter, min.	20 mm
Cable diameter, max.	150 mm	For re-opening	No
Halogen	No	Material	Stainless steel 1.4404 (316L)
Operating temperature range, max.	300 °C	Operating temperature range, min.	-40 °C
Tensile strength	778 N	Tensile strength (Pound-force)	175 lbf

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E524836

Downloads

Catalogues	Catalogues in PDF-format
------------	--

SCT 4.6/520

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

