

THM MT30X 16.5/5.1 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

| | |
|------------|-------------------------------------------|
| Version | THM, Device markers, 5.1 x 16.5 mm, white |
| Order No. | 2799300000 |
| Type | THM MT30X 16.5/5.1 WS |
| GTIN (EAN) | 4064675261070 |
| Qty. | 10,000 pc(s). |

THM MT30X 16.5/5.1 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.08 mm | Depth (inches) | 0.003 inch |
| Height | 5.1 mm | Height (inches) | 0.201 inch |
| Width | 16.5 mm | Width (inches) | 0.65 inch |
| Net weight | 0.025 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

General data

| | | |
|--------------------------------------|-------------------------------|------------|
| Adhesive | Acrylate | |
| Colour | white | |
| Halogen | No | |
| Material | Polyester | |
| Number of markers per combination | 1 Label reel = Device markers | |
| Number of markers per packaging unit | Form of supply | Label reel |
| Operating temperature range | -40...150 °C | |
| Operating temperature range, max. | 150 °C | |
| Operating temperature range, min. | -40 °C | |
| Printed characters | without | |
| UL 94 flammability rating | V-0 | |
| Width | 16.5 mm | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |
| ECLASS 14.0 | 27-28-11-04 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------------------|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

THM MT30X 16.5/5.1 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

