

US67-PLATE64-STD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Knowledge is power - with our Industrial IoT sensors you can record important device data of your existing and new equipment with regard to mechanical and electrical variables. As a result you gain valuable information for important decisions regarding the operation and maintenance of your plants.

General ordering data

Version	Adapter plate
Order No.	2811910000
Type	US67-PLATE64-STD
GTIN (EAN)	4064675292975
Qty.	1 pc(s).

US67-PLATE64-STD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	64 mm	Depth (inches)	2.52 inch
Height	11.5 mm	Height (inches)	0.453 inch
Width	64 mm	Width (inches)	2.52 inch
Diameter	64 mm	Net weight	132 g

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...85 °C
Humidity at operating temperature	5...95 % rel. humidity, no condensation		

General data

Is an accessory	Yes
-----------------	-----

Classifications

ETIM 6.0	EC001068	ETIM 7.0	EC001068
ETIM 8.0	EC001068	ETIM 9.0	EC001068
ECLASS 9.1	19-15-07-90	ECLASS 10.0	19-15-07-90
ECLASS 11.0	19-17-03-04	ECLASS 12.0	19-17-03-04
ECLASS 13.0	19-17-03-04		

Environmental Product Compliance

REACH SVHC	/
------------	---

Downloads

User Documentation	Quick start guide – IS US67-PLATE64-STD
Catalogues	Catalogues in PDF-format

US67-PLATE64-STD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

