

VG 21 HQ MS68 17-20.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated
Order No.	2814780000
Type	VG 21 HQ MS68 17-20.5
GTIN (EAN)	4064675301561
Qty.	1 pc(s).

VG 21 HQ MS68 17-20.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 25 g

Temperatures

Limit temperature -40 °C ... 130 °C

General information

AF size	30 mm	Cable glands	PG 21
Material	Brass, nickel-plated	Protection degree	IP68

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)