

FP DUO DC RC MF SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Energy-efficient emergency lighting with a long service life**

- **developed and to be used in accordance with DIN EN 60598-2-22**
- LED lamp for harsh environmental conditions (shocks and vibration, temperature range)
- higher energy efficiency and service life than fluorescent lamps
- Can be used worldwide thanks to the multi-voltage input (20 V...60 VDC)
- high fire protection classification V0
- Beam direction to two sides
- 5W Power

Versions

- Pluggable with heavy duty connector and round connector
- Pre-assembled 2.5 mm²

General ordering data

Order No.	2815580000
Type	FP DUO DC RC MF SP
GTIN (EAN)	4064675303671

FP DUO DC RC MF SP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	104 mm	Depth (inches)	4.094 inch
Height	121 mm	Height (inches)	4.764 inch
Width	238 mm	Width (inches)	9.37 inch
Net weight	650 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...55 °C
Humidity	92 % @ 25 °C		

General data

Amplitude of acceleration	5 m/s ² (@ 9-200 Hz)	Amplitude of deflection	1.5 mm (2-9 Hz)
Connector cross-section, max.	2.5 mm ²	Connector cross-section, min.	0.5 mm ²
Efficiency class (according to EU Directive No. 874/2012)	E	Halogen	No
Height	≤ 3000 m	Insulation voltage	<500 V (housing/PE)
LED operating life	> 50.000 h	Light colour (CCT)	Cool White, 6000K, 6000K
Light current	496 lm	Light current (in total in both directions)	496 lm
Luminosity	5,000 cd	Mounting position, installation notice	Arbitrary
Peak acceleration, type L	70 m/s ²	Pollution severity	2
Protection class	II	Protection degree	IP67
Rated voltage	24 V	Shape of the LED module	Other
Shock resistance EN 60721-3-3	Class 3M3 portable	Short-circuit protection	Yes, internal
Silicone	No	Surge voltage category	II
Type of connection	Plug-in round connector with fixed number of poles	Type of mounting	Screw mounting
UL 94 flammability rating	V-0	Vibration resistance EN 60721-3-3	Class 3M3 sinusoidal, stationary

Rated data acc. to IEC 60598-1

DC input voltage range	20...60 V DC	Input voltage	20...60 V DC
Power rating	5 W	Rated current	20 mA

Classifications

ETIM 6.0	EC000996	ETIM 7.0	EC000996
ETIM 8.0	EC000996	ETIM 9.0	EC000996
ECLASS 9.1	27-11-06-35	ECLASS 10.0	27-11-06-35
ECLASS 11.0	27-11-06-35	ECLASS 12.0	27-11-06-35
ECLASS 13.0	27-11-06-35	ECLASS 14.0	27-11-06-35

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	4d250b5c-eac1-4909-8961-91bf1e921213

FP DUO DC RC MF SP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E345151

Downloads

Catalogues	Catalogues in PDF-format
------------	--

FP DUO DC RC MF SP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



FP DUO DC RC MF SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****RC-distributor****H-distributor:**

The H distributor is equipped with four poles and impresses with its versatility and IP68 protection class.

General ordering data

Type	RC D 4/4P
Order No.	2819550000
GTIN (EAN)	4064675591290
Qty.	

DC connectors**DC connector:**

The circular connectors of the DC family are characterised by their compact design. This allows them to be used in a wide range of applications and industries. They are available both as male and female connectors.

General ordering data

Type	RC F P2 SP
Order No.	2903200000
GTIN (EAN)	4099986122376
Qty.	

Type	RC M P2 SP
Order No.	2903190000
GTIN (EAN)	4099986122369
Qty.	

FP DUO DC RC MF SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****M20**

Protective caps suitable for FieldPower and WIPL family
with round connector

**General ordering data**

Type	PC RC F
Order No.	2833850000
GTIN (EAN)	4064675591412
Qty.	

Type	PC RC M
Order No.	2820090000
GTIN (EAN)	4064675591405
Qty.	