

IE-USB-A-C-2.0M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A, USB C, PVC, 2 m
Order No.	2838380020
Type	IE-USB-A-C-2.0M
GTIN (EAN)	4064675444329
Qty.	1 pc(s).

IE-USB-A-C-2.0M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	2 m	Length (inches)	78.74 inch
Net weight	57 g		

Temperatures

Operating temperature	-15 °C...80 °C
-----------------------	----------------

Technical specifications for cable

Sheathing colour	black
------------------	-------

Cable structure

Material sheath	PVC	Sheath diameter, max.	3.9 mm
Sheath diameter, min.	3.5 mm	Sheathing colour	black

Plug

Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded	Plug right	IP20, male contact, straight, plug, Plastic, shielded
-----------	--	------------	---

Plug, left

Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded
-----------	--

Plug, right

Plug right	IP20, male contact, straight, plug, Plastic, shielded
------------	---

Classifications

ETIM 6.0	EC001408	ETIM 7.0	EC001408
ETIM 8.0	EC001408	ETIM 9.0	EC001408
ECLASS 9.0	27-06-20-11	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-01-06	ECLASS 11.0	27-06-01-06
ECLASS 12.0	27-06-01-06	ECLASS 13.0	27-06-01-06

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--