

SD ELEC PRO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Test instruments are indispensable when installing, servicing and repairing electrical systems and equipment. Weidmüller has a full range of test devices, including voltage testers, clamp-on meters and power socket/circuit-breaker testers. Weidmüller always takes into account the wishes and experience of users in its development and design work, which means that Weidmüller devices are tailored to the needs of practical applications and are extremely reliable.

General ordering data

Version	Non-contact voltage tester, No
Order No.	2855000000
Type	SD ELEC PRO
GTIN (EAN)	4064675530343
Qty.	1 pc(s).

SD ELEC PRO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	22.2 mm	Depth (inches)	0.874 inch
Width	154.1 mm	Width (inches)	6.067 inch
Diameter	22.2 mm	Net weight	42.5 g

Technical data

Description of article	Srewdriver Voltagetester
------------------------	--------------------------

Measuring and testing devices

AC voltage measuring range	100-250 V	Blade length	63 mm
Blade width (B)	3 mm	Continuity test	No
DC voltage measuring range	230 V	Display	Visual
Frequency range, max.	500 Hz	Frequency range, min.	50 Hz
Working temperature, max.	50 °C	Working temperature, min.	-10 °C

Classifications

ETIM 6.0	EC000494	ETIM 7.0	EC000494
ETIM 8.0	EC000494	ETIM 9.0	EC000494
ECLASS 9.0	27-20-03-08	ECLASS 9.1	27-20-03-08
ECLASS 10.0	27-20-03-08	ECLASS 11.0	27-20-03-08
ECLASS 12.0	27-20-03-08	ECLASS 13.0	27-20-03-08

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--