

**CC-M 15/45 2X3 LRP AL SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	MetalliCard, Device markers, 15 x 45 mm, silver
Order No.	<a href="#">2859680000</a>
Type	CC-M 15/45 2X3 LRP AL SDR
GTIN (EAN)	4064675572572
Qty.	1 pc(s).

**CC-M 15/45 2X3 LRP AL SDR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.5 mm	Depth (inches)	0.02 inch
Height	15 mm	Height (inches)	0.591 inch
Width	45 mm	Width (inches)	1.772 inch
Net weight	0.88 g		

**Temperatures**

Operating temperature range	-55...130 °C
-----------------------------	--------------

**General data**

Colour	silver	
Material	Anodized aluminium	
Number of markers per combination	1 MetalliCard = Device markers	
Number of markers per packaging unit	Form of supply	MetalliCard
Operating temperature range	-55...130 °C	
Operating temperature range, max.	130 °C	
Operating temperature range, min.	-55 °C	
Printed characters	To customer specification	
Size of labelling field	15.2 x 42.2 mm	
Width	45 mm	

**Device markers**

Drill-hole diameter	3.3 mm
---------------------	--------

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CC-M 15/45 2X3 LRP AL SDR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

