

IE-TO-RJ12-C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Mounting rail outlet, RJ12, IP20
Order No.	2861240000
Type	IE-TO-RJ12-C
GTIN (EAN)	4064675579236
Qty.	10 pc(s).

IE-TO-RJ12-C**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	15 g
------------	------

Temperatures

Operating temperature	-40 °C...80 °C
-----------------------	----------------

General data

Connection 1	RJ12	Connection 2	RJ12
Wiring	Coupling	Colour	beige, black
Housing main material	Plastic	Contact surface	Gold over nickel
Type of mounting	TS 35	Shielding	unshielded
Protection degree	IP20	Plugging cycles	≥ 200

General standards

Connector standard	TIA-1096-A
--------------------	------------

Classifications

ETIM 6.0	EC000313	ETIM 7.0	EC000313
ETIM 8.0	EC000313	ETIM 9.0	EC000313
ECLASS 9.0	27-44-03-20	ECLASS 9.1	19-17-01-25
ECLASS 10.0	27-44-03-20	ECLASS 11.0	27-44-03-20
ECLASS 12.0	27-44-03-20	ECLASS 13.0	27-44-03-20

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

IE-TO-RJ12-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

