

WAD 12N MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers.

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|--|
| Version | Group markers, Cover, 33.3 x 12 mm, WDU 16N, white |
| Order No. | 2866660000 |
| Type | WAD 12N MC NE WS |
| GTIN (EAN) | 4064675604877 |
| Qty. | 32 pc(s). |

WAD 12N MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Height | 33.3 mm | Height (inches) | 1.311 inch |
| Width | 12 mm | Width (inches) | 0.472 inch |
| Net weight | 1.238 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | |
|--------------------------------------|-------------------------|-----------|
| Application/manufacture | WDU 16N | |
| Colour | white | |
| Halogen | No | |
| Material | Polyamide 66 | |
| Number of markers per combination | 1 MultiCard = Cover | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Operating temperature range | -40... 100 °C | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| Orientation of print | horizontal and vertical | |
| Printed characters | neutral | |
| UL 94 flammability rating | V-2 | |
| Width | 12 mm | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000761 | ETIM 7.0 | EC000761 |
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ECLASS 9.0 | 27-14-11-37 | ECLASS 9.1 | 27-14-11-37 |
| ECLASS 10.0 | 27-14-11-37 | ECLASS 11.0 | 27-28-11-01 |
| ECLASS 12.0 | 27-28-11-01 | ECLASS 13.0 | 27-28-11-01 |
| ECLASS 14.0 | 27-28-11-01 | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| REACH SVHC | / |
| RoHS Compliance Status | Compliant without exemption |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

WAD 12N MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Drawing