

**FUSE WSFL 22X58 30A 1K5V GPV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	Photovoltaics, Cartridge fuse, 1500 V, 22x58, gPV, 30 A
Order No.	<a href="#">2873880000</a>
Type	FUSE WSFL 22X58 30A 1K5V GPV
GTIN (EAN)	4064675647645
Qty.	10 pc(s).

**FUSE WSFL 22X58 30A 1K5V GPV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	58 mm	Height (inches)	2.283 inch
Width	22 mm	Width (inches)	0.866 inch
Net weight	50 g		

**Temperatures**

Operating temperature range	-40°C ... 90°C
-----------------------------	----------------

**Fuse cartridge**

Fuse-link standard	IEC 60269-6, gPV (EN 60269-6)	Current	30 A
Rated DC voltage	1,500 V	Rated breaking capacity	10 kA
Contact material	silver-plated	Power dissipation, max.	9.8 W

**Classifications**

ETIM 7.0	EC002704	ETIM 8.0	EC002704
ETIM 9.0	EC002704	ECLASS 11.0	27-14-20-02
ECLASS 12.0	27-14-20-02	ECLASS 13.0	27-14-20-02
ECLASS 14.0	27-14-20-02		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## FUSE WSFL 22X58 30A 1K5V GPV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

