

**ESG-LP 9/17 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	ESG, Device markers, 9 x 17 mm, white
Order No.	<a href="#">2885810000</a>
Type	ESG-LP 9/17 MM WS
GTIN (EAN)	4064675854418
Qty.	15,000 pc(s).

**ESG-LP 9/17 MM WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	9 mm	Height (inches)	0.354 inch
Width	17 mm	Width (inches)	0.669 inch
Net weight	0.014 g		

**General data**

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Material	Polyamide
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Printed characters	without	UL 94 flammability rating	V-0
Version	Self-adhesive, halogen-free	Width	17 mm

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Environmental Product Compliance**

REACH SVHC /

**Approvals**

ROHS Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**ESG-LP 9/17 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

