

SD EL 0,6X3,5X60 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Slotted screwdriver with rounded blade SD DIN 5265,
ISO 2380/2, output to DIN 5264, ISO 2380/1. Chrom-
Top tip, SoftFinish grip

General ordering data

Version	Screwdriver, Blade width (B): 35 mm, Blade length: 60 mm, Blade thickness (A): 6 mm
Order No.	2898980000
Type	SD EL 0,6X3,5X60 PICO
GTIN (EAN)	4064675904694
Qty.	1 pc(s).

SD EL 0,6X3,5X60 PICO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	160 mm	Length (inches)	6.299 inch
Diameter	20 mm	Net weight	48 g

Technical data

Description of article	Screwdriver with slotted bit, 0.6 x 3.5	Version	straight
------------------------	---	---------	----------

Screwing tools

Blade length	60 mm	Blade thickness (A)	6 mm
Blade width (B)	35 mm	Form	Slotted

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ETIM 9.0	EC000158
ECLASS 9.0	21-04-04-07	ECLASS 9.1	21-04-04-07
ECLASS 10.0	21-04-04-07	ECLASS 11.0	21-04-04-07
ECLASS 12.0	21-04-04-07	ECLASS 13.0	21-04-04-07
ECLASS 14.0	21-04-04-07		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%