

HSS-HF 1.6-3.2 EL W75M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

Version	TwinMark, Conductor and cable markers, 1.6 - 3.2 mm, white
Order No.	2904840000
Type	HSS-HF 1.6-3.2 EL W75M
GTIN (EAN)	4099986685291
Qty.	1 pc(s).

HSS-HF 1.6-3.2 EL W75M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	0.77 mm	Depth (inches)	0.03 inch
Width	5.6 mm	Width (inches)	0.22 inch
Length	75,000 mm	Length (inches)	2,952.75 inch
Net weight	550 g		

General data

Colour	white
Halogen	No
Length	75,000 mm
Material	Polyolefine
Number of markers per combination	1 Shrink sleeve reel = Conductor and cable markers
Number of markers per packaging unit	Form of supply Shrink sleeve reel
Operating temperature range, max.	105 °C
Operating temperature range, min.	-55 °C
Printed characters	without
Type of printing	neutral
Width	5.6 mm

Conductor and cable markers

Conductor O.D.	1.6 - 3.2 mm	Conductor O.D., max.	3.2 mm
Conductor O.D., min.	1.6 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Cross-section for connected wire	0.5 - 1.5 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

HSS-HF 1.6-3.2 EL W75M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM-HS 60/300 SW	Version
Order No.	2448880000	Ink ribbon
GTIN (EAN)	4050118462944	
Qty.	1 pc(s).	