

## CA 100 DUO S

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Version	Automatic machines, Automatic stripper and crimper
Order No.	<a href="#">2912430000</a>
Type	CA 100 DUO S
GTIN (EAN)	4099986536005
Qty.	1 pc(s).

**CA 100 DUO S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	550 mm	Depth (inches)	21.653 inch
Height	440 mm	Height (inches)	17.323 inch
Width	415 mm	Width (inches)	16.339 inch
Net weight	42,000 g		

**PW65 maintenance - automatic stripping/crimping**

Compressed-air connection	5 - 5.5 bar	Consumables	with plastic collar
Crimping	Trapezoidal	Crimping length	6 - 18 mm
Crimping range, max.	10 mm <sup>2</sup>	Crimping range, min.	4 mm <sup>2</sup>
Drive	Electropneumatic	Electrical connection	100-240 V / 50/60 Hz / 100 VA
Pulse time	approx. 3 s	Stripping range	4 - 6 mm <sup>2</sup> (10 mm <sup>2</sup> opt.) / AWG 12-10 (AWG 8 opt.)
Wire end ferrules cross-section, max.	10 mm <sup>2</sup>	Wire end ferrules cross-section, min.	4 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ECLASS 9.0	17-13-01-01	ECLASS 9.1	17-13-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--