

H0,25/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.comFor conductors from 0.25 to 6,0 mm² (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 7 mm, 7 mm
Order No.	2919620000
Type	H0,25/7
GTIN (EAN)	4099986576742
Qty.	1,000 pc(s).
Packaging	loose

H0,25/7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	7 mm	Height (inches)	0.276 inch
Diameter	1.7 mm	Net weight	0.03 g

Technical data

Description of article	(2)Wire-end ferrule	Version	Standard
------------------------	---------------------	---------	----------

Wire-end ferrules

Collar diameter (D2)	1.7 mm	Conductor cross-section	0.25 mm ²
Contact surface diameter (D1)	0.75 mm	Contact surface length (L2)	7 mm
L1 in mm	7 mm	Stripping length	7 mm
Wire connection cross section AWG, max.	AWG 24		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

H0,25/7

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

