

**KT 40****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

**General ordering data**

Version	Cutting tools
Order No.	<a href="#">2993490000</a>
Type	KT 40
GTIN (EAN)	4099986874312
Qty.	1 pc(s).

## KT 40

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	37 mm	Depth (inches)	1.457 inch
Height	85 mm	Height (inches)	3.346 inch
Width	305 mm	Width (inches)	12.008 inch
Net weight	950 g		

## Cutting tools

Aluminium sector cable	4 x 50 SE	Copper cable - flexible, max.	300 mm <sup>2</sup>
Copper cable - flexible, max. (kcmil)	500 kcmil	Copper cable - stranded, max.	300 mm <sup>2</sup>
Copper cable, max. diameter	40 mm	Copper sector cable	3 x 50 SM
Stranded aluminium cable, max (mm <sup>2</sup> )	300 mm <sup>2</sup>	Stranded aluminium cable, max. (kcmil)	500 kcmil
Stranded aluminium cable, max. diameter	40 mm		

## Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ECLASS 9.0	21-04-47-01	ECLASS 9.1	21-04-90-11
ECLASS 10.0	21-04-47-01	ECLASS 11.0	21-04-47-01
ECLASS 12.0	21-04-47-01	ECLASS 13.0	21-04-47-01

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--