

**HDC 24B ABU EXI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The option of disconnecting cables in the EXI area simplifies installation and servicing and enables better preparation.

The Rockstar<sup>®</sup> EXI enclosures shown here are identified for use by their article designation.

A blue color is therefore not required. A blue EXI gland is required to complete the enclosure.

**General ordering data**

Version	, Size: 8, Protection degree: IP65 (in plugged condition), Bulkhead housing, Side-locking clamp on lower side, Side-locking clamp not replaceable, Standard
Order No.	<a href="#">3001330000</a>
Type	HDC 24B ABU EXI
GTIN (EAN)	4099986902411
Qty.	1 pc(s).

**HDC 24B ABU EXI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	33.8 mm	Height (inches)	1.331 inch
Width	55 mm	Width (inches)	2.165 inch
Mounting dimension - height	32 mm	Mounting dimension - width	130 mm
Net weight	174 g		

**Temperatures**

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

**Dimensions**

Height of base B1	5.3 mm	Height of housing B	30 mm
Hole pitch length A2	130 mm	Total length housing	120 mm
Width base C1	47 mm	Width housing C	43 mm

**General data**

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating	UL 94 flammability rating	V-0
Explosion protection type	II 2G Ex ib IIC T6 Gb		

**Version**

BG	8	Clamp version	Side-locking clamp
Colour (RAL)	RAL 7035	Design	Standard
Design of housing		Design of locking system	Side-locking clamp on lower side, Side-locking clamp not replaceable
	Bulkhead housing		
Sealing	NBR	Size	8
Top part/bottom part/lid	lower part	Type	Bulkhead (feed-through)
Type of connection	PUSH IN		

**Classifications**

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--