

IE-C6OP8LB015CN40N40-B-K4KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled cables with 2x RJ45, suitable for smart metering applications, different colors in accordance with DIN VDE 0603-100. Short plugs and cables with small bending radius for tight spaces, plug housing with circumferential insulation allow protection class IP30 in mated condition.

General ordering data

Version	Patch cable, RJ45 IP30 (plugged), RJ45 IP30 (plugged), Cat. 6, LSZH, 0.15 m, , straight, 4 kV
Order No.	3009730000
Type	IE-C6OP8LB015CN40N40-B-K4KV
GTIN (EAN)	4099986913042
Qty.	1 pc(s).

IE-C6OP8LB015CN40N40-B-K4KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	0.15 m	Length (inches)	5.906 inch
Net weight	20 g		

Temperatures

Operating temperature	-20 °C...70 °C	Installation temperature	0 °C...50 °C
-----------------------	----------------	--------------------------	--------------

Electrical properties

Operating voltage	30 V
-------------------	------

General standards

Application-specific communication cable facilities	VDE-AR-N 4100:2019-04	Connector standard	IEC 60603-7-51
---	-----------------------	--------------------	----------------

Standards

Connector standard	IEC 60603-7-51
--------------------	----------------

Cable structure

Cable layout	Double insulation according to VDE 0603-100	Colour coding	white / blue, white / orange, white / green, white / brown
Complete shielding	Shielding braid made from copper wiring, Aluminium foil	Insulation	PE
Material sheath	LSZH	Number of wires	8
Sheath diameter, max.	4.1 mm	Sheath diameter, min.	3.9 mm
Sheathing colour	blue	Shielding	SF/UTP

Electrical properties of cable

Category	Cat. 6	Operating voltage	30 V
Rated impulse withstand voltage	4 kV	Rated voltage (DC)	30 V

Mechanical and material properties of cable

Colour	blue	Resistance to spread of flame	in accordance with IEC 60332-1-2
--------	------	-------------------------------	----------------------------------

Plug

Plug left	RJ45, IP30 (plugged), male contact, straight, plug, shielded	Plug right	RJ45, IP30 (plugged), male contact, straight, plug, shielded
-----------	--	------------	--

Plug, left

Plug left	RJ45, IP30 (plugged), male contact, straight, plug, shielded
-----------	--

IE-C6OP8LB015CN40N40-B-K4KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Plug, right**

Plug right	RJ45, IP30 (plugged), male contact, straight, plug, shielded
------------	--

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ECLASS 9.0	27-06-03-08	ECLASS 9.1	27-06-03-08
ECLASS 10.0	27-06-03-08	ECLASS 11.0	27-06-03-08
ECLASS 12.0	27-06-03-08	ECLASS 13.0	27-06-03-08
ECLASS 14.0	27-06-03-08		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--