

**PAC-UNIV-HE20-F-2M5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**General ordering data**

Version	Pre-assembled cable, PAC, Cable LiYY, 0.25 mm²
Order No.	<a href="#">7789100025</a>
Type	PAC-UNIV-HE20-F-2M5
GTIN (EAN)	843024395955 1
Qty.	1 pc(s).

## PAC-UNIV-HE20-F-2M5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	270 g
------------	-------

## Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50
---------------------	-------------	-----------------------	----------

## General Data

Cable	Cable LiYY	Cable length	2.5
Connector PLC side	H0.25/10 (FERRULES 0.25mm <sup>2</sup> )	Interface connector	FLAT CABLE CONECTOR HE10 20P
Material	PVC	Number of poles, min.	20-pole
Outer diameter	8.6 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.25 mm <sup>2</sup>		

## Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
High voltage test	1 KV/1s	Operating voltage	≤ 60 V DC ≤ 25 V AC
Permissible current strength per path, max.	1 A	Rated voltage	≤ 60 Vdc ≤ 25 Vac
Resistance	≤ 80 mΩ/m	Total current, max.	3 A

## Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ETIM 9.0	EC000237
ECLASS 9.0	27-24-22-20	ECLASS 9.1	27-24-22-20
ECLASS 10.0	27-24-22-20	ECLASS 11.0	27-24-22-20
ECLASS 12.0	27-24-22-20	ECLASS 13.0	27-24-22-20

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

User Documentation	<a href="#">Colours chart</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>