

CB 430/4,5 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 4.5 x 430 mm, Polyamide 66, 220 N
Order No.	7940006060
Type	CB 430/4,5 NC
GTIN (EAN)	403224852025 1
Qty.	100 pc(s).

CB 430/4,5 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.059 inch
Height	430 mm	Height (inches)	16.929 inch
Width	4.5 mm	Width (inches)	0.177 inch
Net weight	2.92 g		

Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

Installation materials

Bundle diameter, max.	115 mm	Bundle diameter, min.	3.5 mm
Cable diameter, max.	115 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Downloads

Approval/Certificate/Document of Conformity	DE PI830000160627 002
Catalogues	Catalogues in PDF-format

CB 430/4,5 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

