

CB 240/7,8 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 7.8 x 240 mm, Polyamide 66, 540 N
Order No.	7940006067
Type	CB 240/7,8 BK
GTIN (EAN)	4032248524334
Qty.	100 pc(s).

CB 240/7,8 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	1.7 mm	Depth (inches)	0.067 inch
Height	240 mm	Height (inches)	9.449 inch
Width	7.8 mm	Width (inches)	0.307 inch
Net weight	3.42 g		

Temperatures

Operating temperature range	-40...85 °C
-----------------------------	-------------

Installation materials

Bundle diameter, max.	63 mm	Bundle diameter, min.	3.5 mm
Cable diameter, max.	63 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	540 N	Tensile strength (Pound-force)	121 lbf
UL 94 flammability rating	V-2	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Downloads

Approval/Certificate/Document of Conformity	DE PI830000160627 002
Catalogues	Catalogues in PDF-format

CB 240/7,8 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

