

**SP-RS PLC5 1771-G/H/F/FB 21CH, TIN+GOLD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

With increasing plant complexity, the obsolescence of certain PLCs and the relentless growth in demand for I / O signals, many installations or plants are having to replace existing controllers with new ones, without modifying existing field cabling. With the aid of adapters, pre-assembled cables and interfaces from Weidmüller the problem of replacing one PLC system with another can be solved easily and safely: users can maintain the existing field cabling, test the new system and keep installation downtimes to a minimum.

**General ordering data**

Order No.	<a href="#">7940125460</a>
Type	SP-RS PLC5 1771-G/H/F/FB 21CH, TIN+GOLD
GTIN (EAN)	4064675256076
Qty.	1 pc(s).

**SP-RS PLC5 1771-G/H/F/FB 21CH, TIN+GOLD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	144 mm	Depth (inches)	5.669 inch
Height	254 mm	Height (inches)	10 inch
Width	30 mm	Width (inches)	1.181 inch
Net weight	6,248 g		

**Temperatures**

Storage temperature	0...50 °C	Operating temperature	0...50 °C
---------------------	-----------	-----------------------	-----------

**Ratings data**

Operating voltage	240 V	Max. current per channel	3 A
-------------------	-------	--------------------------	-----

**Classifications**

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ETIM 9.0	EC002780
ECLASS 9.0	27-14-11-52	ECLASS 9.1	27-24-22-92
ECLASS 10.0	27-14-11-52	ECLASS 11.0	27-14-11-52
ECLASS 12.0	27-14-11-52	ECLASS 13.0	27-14-11-52

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## SP-RS PLC5 1771-G/H/F/FB 21CH, TIN+GOLD

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

