

FPL 4G2.5/P/Q4MG/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Version	FieldPower®, Cable, Metal housing, Number of wires: 4, Ölflex Classic 110 4G2.5 or similar, Cross-section: 2.5 mm ² , 2 m
Order No.	8000005294
Type	FPL 4G2.5/P/Q4MG/2
GTIN (EAN)	4032248997602
Qty.	1 pc(s).

FPL 4G2.5/P/Q4MG/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	665 g
------------	-------

Technical specifications for cable

Bending radius, min., moving	133.5 mm	Bending radius, min., stationary	35,6 mm
Halogen	Yes	Number of wires	4
Temperature range, moving	-5...70 °C	Temperature range, stationary	-40...70 °C

General technical data

Protection degree	IP65
-------------------	------

Classifications

ETIM 6.0	EC001576	ETIM 7.0	EC001576
ETIM 8.0	EC001576	ETIM 9.0	EC001576
ECLASS 9.0	27-06-04-02	ECLASS 9.1	27-06-91-90
ECLASS 10.0	27-06-04-02	ECLASS 11.0	27-06-04-02
ECLASS 12.0	27-06-04-02	ECLASS 13.0	27-06-04-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1aeccc23-6820-414b-bb61-68f12b86e9f3

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

FPL 4G2.5/P/Q4MG/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

