

**FPL 4G2.5/P/Q4MG/5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

**General ordering data**

Version	FieldPower®, Cable, Metal housing, Number of wires: 4, Ölflex Classic 110 4G2.5 or similar, Cross-section: 2.5 mm <sup>2</sup> , 5 m
Order No.	<a href="#">8000005295</a>
Type	FPL 4G2.5/P/Q4MG/5
GTIN (EAN)	4032248997619
Qty.	1 pc(s).

**FPL 4G2.5/P/Q4MG/5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	1,147 g
------------	---------

**Technical specifications for cable**

Bending radius, min., moving	133.5 mm	Bending radius, min., stationary	35,6 mm
Halogen	Yes	Number of wires	4
Temperature range, moving	-5...70 °C	Temperature range, stationary	-40...70 °C

**General technical data**

Protection degree	IP65
-------------------	------

**Classifications**

ETIM 6.0	EC001576	ETIM 7.0	EC001576
ETIM 8.0	EC001576	ETIM 9.0	EC001576
ECLASS 9.0	27-06-04-02	ECLASS 9.1	27-06-91-90
ECLASS 10.0	27-06-04-02	ECLASS 11.0	27-06-04-02
ECLASS 12.0	27-06-04-02	ECLASS 13.0	27-06-04-02

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1aeccc23-6820-414b-bb61-68f12b86e9f3

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## FPL 4G2.5/P/Q4MG/5

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

