

TS15X5 ST MPC0712 VER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Similar to illustration

Accessories

General ordering data

Version	Rail, TS 15, Width: 55 mm, without slot, Steel, galvanized, chromium-plated
Order No.	8000037599
Type	TS15X5 ST MPC0712 VER
GTIN (EAN)	4050118653113
Qty.	20 pc(s).

TS15X5 ST MPC0712 VER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	5.5 mm	Depth (inches)	0.217 inch
Height	15 mm	Height (inches)	0.591 inch
Width	55 mm	Width (inches)	2.165 inch
Net weight	11 g		

General information

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Material thickness	1 mm
Standards	DIN EN 60715	Surface finish	galvanized, chromium-plated

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format