

**TS15X5 ST FPC 20 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Similar to illustration

Accessories

**General ordering data**

Version	Rail, TS 15, Width: 235 mm, without slot, Steel, galvanized, chromium-plated
Order No.	<a href="#">8000037604</a>
Type	TS15X5 ST FPC 20 VER
GTIN (EAN)	4050118653168
Qty.	20 pc(s).

**TS15X5 ST FPC 20 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	5.5 mm	Depth (inches)	0.217 inch
Height	15 mm	Height (inches)	0.591 inch
Width	235 mm	Width (inches)	9.252 inch
Net weight	29.95 g		

**General information**

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Material thickness	1 mm
Standards	DIN EN 60715	Surface finish	galvanized, chromium-plated

**Classifications**

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>