

**TS35 MPC 1717 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Similar to illustration

Accessories

**General ordering data**

Version	Rail, TS 35 x 7.5, TS 35, Width: 106 mm, without slot, Steel, galvanized, chromium-plated
Order No.	<a href="#">8000037605</a>
Type	TS35 MPC 1717 VER
GTIN (EAN)	4050118653175
Qty.	20 pc(s).

**TS35 MPC 1717 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	106 mm	Width (inches)	4.173 inch
Net weight	21.733 g		

**General information**

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Standards	DIN EN 60715
Surface finish	galvanized, chromium-plated		

**Classifications**

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--