

KLIPPON POK 252512 FH M32 E60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Fire-resistant terminal boxes E30, E60 and E90**

Robust terminal box for safe power supply of emergency systems in case of fire, emergency lighting in underground, metro, railway and road tunnels up to a maximum of 90 minutes according to DIN 4102-04. The equipped enclosures of the Klippon® POK and Klippon® STB series are suitable wherever corrosion resistance, impact resistance and a high degree of protection is required.

Features:

- Available in a wide variety of designs on customer request
- Tested and approved according to DIN 4102-04 (E30, E60 and E90) - The exact details must be taken from the "Declaration of Manufacturer"
- High quality through the use of proven basic products of the Klippon® brand

General ordering data

| | |
|-------------------|--|
| Version | Klippon POK (polyester empty enclosure), Enclosures, Height: 250 mm, Width: 255 mm, Depth: 120 mm, Material: Glass fibre-reinforced polyester, untreated, grey, Light Grey |
| Order No. | 8000054731 |
| Type | KLIPPON POK 252512 FH M32 E60 |
| GTIN (EAN) | 4064675362333 |
| Qty. | 1 pc(s). |
| Reference product | 1305930000 0122800000 0236400000 9502610000 9502650000 0303000000 9502630000 9509510000 0445600000 2007170000 1909720000 1736260000 1772480000 |

KLIPPON POK 252512 FH M32 E60**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|----------------------------|-------------|-----------------------------|------------|
| Depth | 120 mm | Depth (inches) | 4.724 inch |
| Height | 250 mm | Height (inches) | 9.842 inch |
| Height of lowest version | 120 mm | Width | 255 mm |
| Width (inches) | 10.039 inch | Mounting dimension - height | 200 mm |
| Mounting dimension - width | 235 mm | Net weight | 4,787.19 g |

Temperatures

| | |
|-----------------------|----------------|
| Operating temperature | -20 °C...80 °C |
|-----------------------|----------------|

horizontal assembly

| | | | |
|---------|---|-----------------------|-----|
| SAKK 10 | 8 | Fuse holder available | Yes |
|---------|---|-----------------------|-----|

Housing

| | | | |
|--------------------|----------------------------------|--------------------|---------|
| Drill holes side A | 1 x M32 | Drill holes side B | 2 x M32 |
| Material | Glass fibre-reinforced polyester | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002503 | ETIM 7.0 | EC002503 |
| ETIM 8.0 | EC002503 | ETIM 9.0 | EC002503 |
| ECLASS 9.0 | 27-18-05-02 | ECLASS 9.1 | 27-18-05-02 |
| ECLASS 10.0 | 27-18-05-02 | ECLASS 11.0 | 27-18-05-02 |
| ECLASS 12.0 | 27-18-05-02 | ECLASS 13.0 | 27-18-05-02 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1d28ada4-1634-4382-8635-45f6353a6574 |

Important note

| | |
|---------------------|--|
| Product information | The fire rating up to E60 acc. to DIN 4102-12 depends on concrete configurations / installations (details see "Declaration of Manufacturer" in "Downloads") The enclosure is used for functional integrity and serves as a distribution box for cables with 4 potentials. |
|---------------------|--|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | MPA NRW Certificate - fire rated assembled boxes acc. to DIN 4102-12 DoM DE PS2510 210414 001ISS00 - Fire Rated Boxes |
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

KLIPPON POK 252512 FH M32 E60

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Similar to illustration

