


PVC AC 1I 10 SPD2R + RJ45 04**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	AC voltage version, Auxiliary and alarm contact, TN-C-S, TN-S, IT with N, IT without N, TT
Order No.	8000104168
Type	PVC AC 1I 10 SPD2R + RJ45 04
GTIN (EAN)	4099986573475
Qty.	1 pc(s).

PVC AC 1I 10 SPD2R + RJ45 04

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	132 mm	Depth (inches)	5.197 inch
Height	200 mm	Height (inches)	7.874 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	2,100.243 g		

Temperatures

Operating temperature	-25 °C...50 °C
-----------------------	----------------

Rated data IEC / EN

Discharge current I_n (8/20µs) wire-PE	20 kA	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Low voltage network	TN-C-S, TN-S, IT with N, IT without N, TT
Max. continuous voltage, U_c (AC)	300 V	Number of poles	4
Protection level U_p at I_N (L/N-PE)	≤ 1.5 kV	Protection level U_p at I_N (N-PE)	≤ 1.5 kV
Rated voltage (AC)	230 V	Short-circuit current rating I_{SCCR}	50 kA
Signalling contact	250 V 1A 1CO	Voltage type	AC

AC inputs

Connection cross-section, stranded, max.	6 mm ²	Connection cross-section, stranded, min.	0.34 mm ²
Connection type, AC input cable	PUSH IN	Number of AC inputs	3
Stripping length, rated connection	12 mm	Wire cross-section, solid, max.	6 mm ²
Wire cross-section, solid, min.	0.5 mm ²		

AC outputs

Connection cross-section, stranded, max.	6 mm ²	Connection cross-section, stranded, min.	0.34 mm ²
Stripping length, rated connection	12 mm	Wire cross-section, solid, max.	6 mm ²
Wire cross-section, solid, min.	0.5 mm ²		

Guarantee

Time interval	5 years
---------------	---------

General data

Protection degree	IP65
-------------------	------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ETIM 9.0	EC000941
ECLASS 9.0	27-13-08-05	ECLASS 9.1	27-13-08-05
ECLASS 10.0	27-13-08-05	ECLASS 11.0	27-13-08-05
ECLASS 12.0	27-17-90-90	ECLASS 13.0	27-17-90-90
ECLASS 14.0	27-17-90-90		

PVC AC 1I 10 SPD2R + RJ45 04

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	bdab5698-6a20-4370-8e28-8810d882d01a
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Technical Documentation	Schematic diagram
Catalogues	Catalogues in PDF-format

PVC AC 1I 10 SPD2R + RJ45 04

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

