

FBCON PA CG 1WAY EX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

For applications in hazardous areas, PROFIBUS PA Ex junction boxes are available as 1-way, 2-way, 4-way, and 8-way distributors.

EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Protection class IP66
- Aluminium versions
- Profibus PA compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

General ordering data

Version	Standard distributor for Ex applications EEx(ia), 1-way distributor EEx, IP66
Order No.	8564180000
Type	FBCON PA CG 1WAY EX
GTIN (EAN)	4032248236589
Qty.	1 pc(s).

FBCON PA CG 1WAY EX

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	37 mm	Height (inches)	1.457 inch
Width	58 mm	Width (inches)	2.283 inch
Length	64 mm	Length (inches)	2.52 inch
Net weight	259 g		

Temperatures

Storage temperature	-40 °C...80 °C	Ambient temperature	-40 °C...80 °C
Operating temperature	-40 °C...80 °C		

Technical data

Bus system	Profibus-PA, Foundation Fieldbus	Cable entry	Brass cable gland
Conductor O.D., max.	9.5 mm	Conductor O.D., min.	5.5 mm
Connection type PE	Spur line with cable gland	Contact carrier material	Brass
Contact material	CuZnAu	Design of housing	With pressure compensation element
Housing main material	Aluminium, AlSi12	Number of contact sockets	1
Pollution severity	2	Protection degree	IP66
Type of distribution	1-way distributor EEx	Type of mounting	surface-mounted, Front mounting

Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-24-26-08
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3a5f5913-76fc-4ff5-8563-4463f80bbe02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

FBCON PA CG 1WAY EX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	Certification ATEX Declaration of Conformity
Engineering Data	CAD data – STEP
Product Change Notification	20220208 Technical change to FBCon field distributors (passive, with aluminum housings)
Software	WI-Segment-Calculator
User Documentation	Instruction sheet Application-Guide-Planning and installing Fieldbus networks-using-FBCon_english_deutsch
Catalogues	Catalogues in PDF-format
Brochures	

FBCON PA CG 1WAY EX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

