

**SCM 4CO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****General ordering data**

Version	RIDERSERIES RCM, Relay socket, Number of contacts: 4, CO contact, Continuous current: 12 A, Screw connection
Order No.	<a href="#">8690900000</a>
Type	SCM 4CO
GTIN (EAN)	4032248361564
Qty.	10 pc(s).

## SCM 4CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	61.5 mm	Depth (inches)	2.421 inch
Height	77 mm	Height (inches)	3.031 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	69.094 g		

## Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-45 °C...70 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

## Rated data UL

Certificate No. (cURus)	E223759
-------------------------	---------

## Load side

Rated switching voltage	250 V AC	Continuous current	12 A
Max. switching voltage, AC	300 V	AC switching capacity (resistive), max.	3000 VA
Contact type	4 CO contact		

## General data

Rail	TS 35	Colour	black
------	-------	--------	-------

## Insulation coordination

Dielectric strength, Input/Output	2.5 kV <sub>eff</sub> / 1 Min.	Protection degree	IP20
-----------------------------------	--------------------------------	-------------------	------

## Further details of approvals / standards

Standards	UL508	Certificate No. (cURus)	E223759
-----------	-------	-------------------------	---------

## Connection data

Wire connection method	Screw connection	Tightening torque, min.	0.5 Nm
Tightening torque, max.	0.8 Nm	Clamping range, rated connection	2.5 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2.5 mm <sup>2</sup>
Blade size	size PH1		

## Classifications

ETIM 6.0	EC001456	ETIM 7.0	EC001456
ETIM 8.0	EC001456	ETIM 9.0	EC001456
ECLASS 9.0	27-37-16-03	ECLASS 9.1	27-37-16-03
ECLASS 10.0	27-37-16-03	ECLASS 11.0	27-37-16-03
ECLASS 12.0	27-37-16-03	ECLASS 13.0	27-37-16-03

**SCM 4CO****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223759

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">EU Konformitätserklärung / EU Declaration of Conformity</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## SCM 4CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Individual components



Relay modules with forcibly guided contacts

Relays with forcibly guided contacts have a 99 % diagnostics coverage and an excellent reputation for use in safety systems. The contacts interlock mechanically with each other in order to ensure a synchronous switching status of both contacts. This guarantees that the alert contact will maintain the same switching status in the event of an error (for example, if the working contact welds from an overload). The controller (or safety controller) detects the alert contact and then compares the set values and actual values. If a difference occurs, measures can then be taken to protect equipment and human life.

- 2 CO contacts with 6 A, forcibly guided according to EN 61810-3 type B
- Proven component in safety technology
- Diagnosis coverage of 99 %

## General ordering data

Type	RIM 2 6/24VDC GN	Version
Order No.	<a href="#">8713720000</a>	RIDERSERIES FG, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248389872	voltage: 6...24 V DC, Plug-in connection
Qty.	10 pc(s).	

## RCM

## General ordering data

Type	SCM CLIP M	Version
Order No.	<a href="#">8691100000</a>	RIDERSERIES RCM, Retaining clip
GTIN (EAN)	4032248361809	
Qty.	10 pc(s).	
Type	SCM CLIP P	Version
Order No.	<a href="#">8691110000</a>	RIDERSERIES RCM, Retaining clip
GTIN (EAN)	4032248361816	
Qty.	10 pc(s).	

## SCM 4CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## RCL

## General ordering data

Type	RIM 2 110/230VDC GN	Version
Order No.	<a href="#">8713740000</a>	RIDERSERIES RCL, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248390113	voltage: 110...230 V DC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 3 6/24VAC	Version
Order No.	<a href="#">8690980000</a>	RIDERSERIES RCL, LED module, Rated control voltage: 6 V AC, 24 V
GTIN (EAN)	4032248361663	AC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 3 24/60VAC	Version
Order No.	<a href="#">8690990000</a>	RIDERSERIES RCL, LED module, Rated control voltage: 24...60 V AC,
GTIN (EAN)	4032248361670	Plug-in connection
Qty.	10 pc(s).	
Type	RIM 1 6/230V	Version
Order No.	<a href="#">8690940000</a>	RIDERSERIES RCL, Free-wheeling diode, Rated control voltage: 6...230
GTIN (EAN)	4032248361601	V, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 2 24/60VDC	Version
Order No.	<a href="#">8690960000</a>	RIDERSERIES RCL, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248361649	voltage: 24...60 V DC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 1 R 110/230V	Version
Order No.	<a href="#">8816590000</a>	RIDERSERIES RCL, Load
GTIN (EAN)	4032248516803	
Qty.	10 pc(s).	
Type	RIM 2 24/60VDC GN	Version
Order No.	<a href="#">8713730000</a>	RIDERSERIES RCL, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248389889	voltage: 24...60 V DC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 4 6/24VUC GN	Version
Order No.	<a href="#">8713780000</a>	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248390151	voltage: 6...24 V UC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 3 24/60VUC	Version
Order No.	<a href="#">8691020000</a>	RIDERSERIES RCL, LED module, Rated control voltage: 24...60 V UC,
GTIN (EAN)	4032248361700	Plug-in connection
Qty.	10 pc(s).	
Type	RIM 3 24/60VUC GN	Version
Order No.	<a href="#">8713760000</a>	RIDERSERIES RCL, LED module, Rated control voltage: 24...60 V UC,
GTIN (EAN)	4032248390137	Plug-in connection
Qty.	10 pc(s).	

Creation date June 1, 2024 10:11:16 PM CEST

## SCM 4CO

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	RIM 4 6/24VUC	Version
Order No.	<a href="#">8691040000</a>	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248361724	voltage: 6...24 V UC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 2 6/24VDC	Version
Order No.	<a href="#">8690950000</a>	RIDERSERIES RCL, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248361632	voltage: 6...24 V DC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 3 6/24VUC GN	Version
Order No.	<a href="#">8713750000</a>	RIDERSERIES RCL, LED module, Rated control voltage: 6...24 V UC,
GTIN (EAN)	4032248390120	Plug-in connection
Qty.	10 pc(s).	
Type	RIM 3 110/230VUC	Version
Order No.	<a href="#">8691030000</a>	RIDERSERIES RCL, LED module, Rated control voltage: 110...230 V
GTIN (EAN)	4032248361717	UC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 3 110/230VUC GN	Version
Order No.	<a href="#">8713770000</a>	RIDERSERIES RCL, LED module, Rated control voltage: 110...230 V
GTIN (EAN)	4032248390144	UC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 4 110/230VUC GN	Version
Order No.	<a href="#">8713800000</a>	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248390182	voltage: 110...230 V UC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 4 24/60VUC	Version
Order No.	<a href="#">8691050000</a>	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248361731	voltage: 24...60 V UC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 4 24/60VUC GN	Version
Order No.	<a href="#">8713790000</a>	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248390168	voltage: 24...60 V UC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 2 110/230VDC	Version
Order No.	<a href="#">8690970000</a>	RIDERSERIES RCL, LED module with freewheel diode, Rated control
GTIN (EAN)	4032248361656	voltage: 110...230 V DC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 4 110/230VUC	Version
Order No.	<a href="#">8691060000</a>	RIDERSERIES RCL, LED module, Protective varistor, Rated control
GTIN (EAN)	4032248361748	voltage: 110...230 V UC, Plug-in connection
Qty.	10 pc(s).	
Type	RIM 3 110/230VAC	Version
Order No.	<a href="#">8691000000</a>	RIDERSERIES RCL, RC filter, Rated control voltage: 110...230 V AC,
GTIN (EAN)	4032248361687	Plug-in connection
Qty.	10 pc(s).	