

SCHUKO TS35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Simple installation in electrical cabinet
- TS35 module can be mounted on rail
- VDE mark of conformity
- Two-pole with earthing contact

General ordering data

Version	Electrical-cabinet socket outlet TS 35
Order No.	8734580000
Type	SCHUKO TS35
GTIN (EAN)	4032248407835
Qty.	10 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2024-08-03

SCHUKO TS35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	45 mm	Height (inches)	1.772 inch
Width	76 mm	Width (inches)	2.992 inch
Length	60 mm	Length (inches)	2.362 inch
Net weight	95 g		

Temperatures

Storage temperature	-20 °C...40 °C	Operating temperature	-20 °C...40
---------------------	----------------	-----------------------	-------------

Input

Rated current	16 A
---------------	------

General data

Colour	beige	Design	Installation housing
Rail	TS 35		

Insulation coordination

Pollution severity	2	Surge voltage category	II
--------------------	---	------------------------	----

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	II
--------------------	---	------------------------	----

Classifications

ETIM 6.0	EC000125	ETIM 7.0	EC000125
ETIM 8.0	EC000125	ETIM 9.0	EC000125
ECLASS 9.0	27-14-40-42	ECLASS 9.1	27-14-40-42
ECLASS 10.0	27-14-40-42	ECLASS 11.0	27-14-40-42
ECLASS 12.0	27-14-40-42	ECLASS 13.0	27-14-40-42
ECLASS 14.0	27-14-40-42		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Creation date November 10, 2024 8:47:05 PM CET

Catalogue status 26.10.2024 / We reserve the right to make technical changes.

SCHUKO TS35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIS SL 0.6X3.5X100	Version
Order No.	1274660000	Screwdriver, Mounting tool
GTIN (EAN)	4050118072631	
Qty.	1 pc(s).	

W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type	WEW 35/1 V0 GF SW	Version
Order No.	1478990000	End bracket, black, TS 35, V-0, Wemid, Width: 12 mm, 130 °C
GTIN (EAN)	4050118286892	
Qty.	50 pc(s).	
Type	WEW 35/2 V0 GF SW	Version
Order No.	1479000000	End bracket, black, TS 35, V-0, Wemid, Width: 8 mm, 130 °C
GTIN (EAN)	4050118286779	
Qty.	50 pc(s).	

SCHUKO TS35

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crosshead screwdriver, Pozidrive



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Type	SDIK PZ1 SL	Version
Order No.	1274730000	Screwdriver, Screwdriver
GTIN (EAN)	4050118073225	
Qty.	1 pc(s).	