

IE-C7BS8VG-100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Bulk stock, copper cable, rigid, 4 x 2 x AWG 23/1, Cat. 7,
green

General ordering data

Version	Installation cable, Cat.7 (ISO/IEC 11801), PVC, 100 m
Order No.	8813130000
Type	IE-C7BS8VG-100
GTIN (EAN)	4032248512881
Qty.	1 pc(s).
Packaging	as cable ring in carton

IE-C7BS8VG-100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	100 m	Length (inches)	3,937.008 inch
Net weight	6,490 g		

Temperatures

Storage temperature	-40 °C...75 °C	Operating temperature	-40 °C...75 °C
Installation temperature	0 °C...50 °C		

Technical specifications for cable

Insulation	PE	Number of poles	8
Number of wires		Resistance to spread of flame	in accordance with IEC 60332-1, EN 13501-6 class FCa
	8		
Sheathing colour	green (RAL 6018)	Test voltage: wire-wire-shield	700 V AC

Cable specific standards

Corrosiveness of fumes	to IEC 60754-2	Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
------------------------	----------------	--	---------------------------------------

Standards

Corrosiveness of fumes	to IEC 60754-2	Generic communication cable facilities	EN 50173-1:2007, ISO / IEC 11801:2002
------------------------	----------------	--	---------------------------------------

Cable structure

Arrangement of wire cores		Colour sequence or wires - wire pairs	white - blue, white - orange, white - green, white - brown
	Twisted pair		
Complete shielding	Shielding braid made from copper wiring	Cross-section	4*2*AWG 23/1 - 4*2*0.255 mm ²
Insulation	PE	Insulation cross-section	1.4 mm
Material sheath	PVC	Number of wires	8
Sheath diameter, max.	8 mm	Sheath diameter, min.	7.6 mm
Sheathing colour	green (RAL 6018)	Sheathing material thickness	0.8 mm
Shielding	S/FTP	Shielding braid thickness	0.1 mm
Standard designations	IE-7IC4x2xAWG23/1-PVC 02YSCY PIMF, S/FTP	Strands	1
Wire material	Non-insulated copper wire	Wire pair shielding	Aluminium foil

Electrical properties of cable

Capacity at 1 kHz	45 nF/km	Category	Cat.7 (ISO/IEC 11801)
Characteristic impedance	100 ± 5 Ω at 100MHz	Delay skew	5 ns/100m
Loop resistance	150 Ω/km	Shield attenuation	85 dB at 600 Mhz
Signal propagation time	4.25 ns/m	Test voltage: wire-wire-shield	700 V AC
Transfer impedance	6 mΩ/m at 1 MHz, 3 mΩ/m at 10 MHz, 3 mΩ/m at 30 MHz		

IE-C7BS8VG-100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Mechanical and material properties of cable

Abrasion resistance	good	Colour	green
Corrosiveness of fumes	to IEC 60754-2	Min. bending radius, once only	4 x cable diameter
Min. bending radius, repetitive	8 x cable diameter	Pulling force	120 N
Resistance to spread of flame	in accordance with IEC 60332-1, EN 13501-6 class FCa	Silicone-free	Yes
UV-resistant	Yes		

Classifications

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ETIM 9.0	EC003249
ECLASS 9.0	27-06-18-05	ECLASS 9.1	27-06-90-90
ECLASS 10.0	27-06-18-01	ECLASS 11.0	27-06-18-01
ECLASS 12.0	27-06-18-01	ECLASS 13.0	27-06-18-01

Approvals

Approvals



ROHS

Conform

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-C7BS8VG-100

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Detailed drawing



IE-C7BS8VG-100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Tools**

Sheathing stripper for PVC cables

**General ordering data**

Type	AM 12	Version
Order No.	9030060000	Tools, Sheathing strippers
GTIN (EAN)	4008190337827	
Qty.	1 pc(s).	

Tools

The CST with blue blade cartridge produces the best stripping results.
The blue double-stage blade cartridge is particularly suited for Ethernet cables. It saves time and also ensures optimal stripping results.

General ordering data

Type	IE-CST	Version
Order No.	9204350000	Tools, Sheathing strippers
GTIN (EAN)	4032248653072	
Qty.	1 pc(s).	