

IE-FM6D2UE0003MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 62.5 µm

General ordering data

| | |
|------------|-------------------------------------------------|
| Version | Dragline cable, ST, ST IP 20, 62.5 µm, PUR, 3 m |
| Order No. | 8876460030 |
| Type | IE-FM6D2UE0003MST0ST0X |
| GTIN (EAN) | 4032248610044 |
| Qty. | 1 pc(s). |

IE-FM6D2UE0003MST0ST0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Length | 3 m | Length (inches) | 118.11 inch |
| Net weight | 100 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|-------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...80 |
| Installation temperature | -20 °C...60 °C | | |

General standards

| | |
|--------------------|-------------|
| Connector standard | IEC 61754-2 |
|--------------------|-------------|

Standards

| | |
|--------------------|-------------|
| Connector standard | IEC 61754-2 |
|--------------------|-------------|

Cable structure

| | | | |
|-----------------|--------------------|------------------|---------|
| Cable layout | Break-out dragline | Core diameter | 62.5 µm |
| Material sheath | PUR | Primary coating | 245 µm |
| Sheath diameter | 6 mm | Sheathing colour | black |

Mechanical and material properties of cable

| | | | |
|---------------------------------|---------|--------------------------------|-------|
| Bending cycles | 100,000 | Min. bending radius, once only | 25 mm |
| Min. bending radius, repetitive | 77 mm | | |

Plug

| | | | |
|-----------|-------------------------------------------------------------|------------|-------------------------------------------------------------|
| Plug left | ST, IP20, male contact, straight, plug, Plastic, unshielded | Plug right | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|-----------|-------------------------------------------------------------|------------|-------------------------------------------------------------|

Plug, left

| | |
|-----------|-------------------------------------------------------------|
| Plug left | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|-----------|-------------------------------------------------------------|

Plug, right

| | |
|------------|-------------------------------------------------------------|
| Plug right | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|------------|-------------------------------------------------------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002607 | ETIM 7.0 | EC002607 |
| ETIM 8.0 | EC002607 | ETIM 9.0 | EC002607 |
| ECLASS 9.0 | 27-06-10-03 | ECLASS 9.1 | 27-06-10-03 |
| ECLASS 10.0 | 27-06-10-03 | ECLASS 11.0 | 27-06-10-03 |
| ECLASS 12.0 | 27-06-10-03 | ECLASS 13.0 | 27-06-10-03 |

IE-FM6D2UE0003MST0ST0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Environmental Product Compliance**

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|-----------------------------------------------------------------------------------------------------------------------|
| User Documentation | MAN IE GUIDE DE MAN IE GUIDE EN |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN |

IE-FM6D2UE0003MST0ST0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Detailed drawing

