

MEHA KP BL M-D-SPX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

General ordering data

Version	Accessories, Set of cutters
Order No.	9003630000
Type	MEHA KP BL M-D-SPX
GTIN (EAN)	4008190094256
Qty.	1 pc(s).

MEHA KP BL M-D-SPX**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	16 mm	Depth (inches)	0.63 inch
Height	11.5 mm	Height (inches)	0.453 inch
Width	26 mm	Width (inches)	1.024 inch
Net weight	3.68 g		

Technical data

Description of article	Set of blades for Mini-Duro-Stripax up to AWG 20 for PTFE
------------------------	-----------------------------------------------------------

Stripping tools

Cable type	Conductor with custom insulation	Colour	blue
Max. conductor diameter	0.92 mm	Min. conductor diameter	0.88 mm
Stripping length, max.	7 mm	Stripping length, min.	3 mm

Classifications

ETIM 6.0	EC001509	ETIM 7.0	EC001509
ETIM 8.0	EC001509	ETIM 9.0	EC001509
ECLASS 9.0	21-04-92-37	ECLASS 9.1	21-04-48-90
ECLASS 10.0	21-04-92-37	ECLASS 11.0	21-04-48-91
ECLASS 12.0	21-04-48-91	ECLASS 13.0	21-04-48-91

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	