

**H35,0/32****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

For conductors from 10.0 to 185.0 mm<sup>2</sup> (AWG 7 - 350 MCM)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in poly-bag

**General ordering data**

Version	Wire-end ferrule, Standard, 32 mm, 32 mm, No
Order No.	<a href="#">9004200000</a>
Type	H35,0/32
GTIN (EAN)	4008190077303
Qty.	100 pc(s).
Packaging	loose

**H35,0/32****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	1.61 g
------------	--------

**Technical data**

Description of article	Wire end ferrule without plastic collar, (2)Wire-end ferrule	Version	Standard
------------------------	--	---------	----------

**Wire-end ferrules**

Collar diameter (D2)	11 mm	Conductor cross-section	35 mm <sup>2</sup>
Contact surface diameter (D1)	8.3 mm	Contact surface length (L2)	32 mm
L1 in mm	32 mm	Stripping length	32 mm
Wire connection cross section AWG, max.	AWG 2		

**Classifications**

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**H35,0/32**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

